

Digitrax Decoder Index

DH84FX

Photo

DH84FX Instructions [Digitrax Decoder Manual](#)

| | | | |
|----------------------|--|-----------------------|-----------------|
| Physical Size | 0.67" x 1.2" x 0.25" 17.02mm x 30.48mm x 6.35mm | Current Rating | 1.0/1.5 |
| Interface | Decoder End | Wires | End/Plug |
| D | DTX 9 | 7" | 177mm Wires |

| | | | | | |
|--------------------|------------|--------------------------------|------------|----------------------|---|
| # Functions | 4 | Function Current Rating | 200mA | Function Type | FX |
| Prod Date | 02-01-1996 | Discontinued | 03-18-1997 | Replaced By | DH163 DH142 DH140 |

[FX Motor Isolation Protection Note](#)

| CV# | Feature | Default | Range | Notes |
|--|-----------------------------------|---------|--------------------------|--|
| 2 Digit and 4 Digit Addressing | | | | |
| 01 | 2 Digit Decoder Address | 003/x03 | 001-127 | |
| 17 | 4 Digit Address Hi Byte | 000/x00 | 0128-9983 | CV17 & 18 are used together |
| 18 | 4 Digit Address Lo Byte | 000/x00 | 0128-9983 | |
| 29 | Configuration Register | 006/x06 | Table 29 | |
| Configuration Register | | | | |
| 29 | Configuration Register | 006/x06 | Table 29 | |
| | Address Selection, 2 or 4 digit | 2 Digit | 2 or 4 Digit | |
| | Normal Direction of Travel (NDOT) | | | Not Available |
| | Speed Step Control | 28/128 | 14 or 28/128 | |
| | Speed Table On/Off | Off | Speed Table On or Off | |
| | Analog Mode Conversion On/Off | On | On or Off | |
| LocoMotion™ | | | | |
| Acceleration & Deceleration | | | | |
| 03 | Acceleration Rate | 000/x00 | 000/x00 to 031/x1F | 128 Steps |
| 04 | Deceleration Rate | 000/x00 | 000/x00 to 031/x1F | 128 Steps |
| Three Step Speed Table & Start Voltage | | | | |
| 02 | Start Voltage | 000/x00 | 000/x00 to 255/xFF | 128 Steps |
| 05 | Maximum Voltage | 000/x00 | 000/x00 to 255/xFF | 28 Steps 000/x00, 001/x01 & 255/xFF= max voltage at step 28 |
| 06 | Mid Point Voltage | 000/x00 | 000/x00 to 255/xFF | 28 Steps 000/x00 & 001/x01= straight line curve |
| 28 Step Speed Tables-28 steps | | | | |
| 65 | Kick Start value | 000/x00 | | 28 Steps |
| 66 | Forward Trim | 000/x00 | | 28 Steps |
| 67 | First Speed Table Entry | 000/x00 | | 28 Steps |
| 68-93 | 28 Step Speed Table Entries | 000/x00 | | 28 Steps |
| 94 | Maximum Speed Table Step | 000/x00 | | 28 Steps |

| | | | | |
|---|--|-------------|----------------------------------|----------------------------|
| 95 | Reverse Trim | 000/x00 | | 28 Steps |
| 29 | Configuration Register | 006/x06 | Table 29 | Set to enable speed tables |
| Torque Compensation & Switching Speed | | | | |
| 53 | Used for FX Function Control | | | Not Available |
| 54 | Torque Compensation Switching Speed | | | Not Available |
| DC Functions | | | | |
| 13 | DC Functions ON | | | Not Available |
| FX Functions | | | | |
| 49 | F0F, forward light effect white | 000/x00 | FX Effects Table | |
| 50 | F0R, reverse light effect yellow | 000/x00 | FX Effects Table | |
| 51 | F1, Function 1 green | 000/x00 | FX Effects Table | |
| 52 | F2, Function 2 violet | 000/x00 | FX Effects Table | |
| 53 | F3, Function 3 brown | | | Not Available |
| 54 | F4, function 4 white/yellow | | | Not Available |
| 115 | F5, Function F5 white/green | | | Not Available |
| 116 | F6, Function F6 white/blue | | | Not Available |
| 62 | FX Rate and Keep alive adjust | 000/x00 | 000/x00 to 255/xFF | |
| 63 | Ditch Light Blink hold time | 000/x00 | 000/x00 to 255/xFF | |
| Directional Headlights, Transponding, Split Field Motor | | | | |
| 61 | Directional Headlight | Directional | Table 61 | |
| | Transponding | | | Not Available |
| | Split Field Motor | | | Not Available |
| Scaleable Speed Stabilization | | | | |
| 55 | Static Compensation | | | Not Available |
| 56 | Dynamic Compensation | | | Not Available |
| 57 | Speed Stabilizer-Droop | | | Not Available |
| SuperSonic | | | | |
| 09 | Motor Frequency SuperSonic | | | Not Available |
| Advanced Consisting | | | | |
| 19 | Advanced Consist Address | | | Not Available |
| 21 | Advanced Consist Function Control Override for F1-F8 | | | Not Available |
| 22 | Advanced Consist Function Control Override for F0 & F9-F12 | | | Not Available |
| Function Remapping | | | | |
| 33-46 | Function Remapping CVs | | | Not Available |
| Decoder Factory Reset | | | | |
| 08 | Reset Decoder to Factory Default CV Values | | | Not Available |
| IDs | | | | |
| 105 | User Private ID #1 | 000/x00 | | |
| 106 | User Private ID #2 | 000/x00 | | |
| 07 | Version ID | Various | 000 & others | Read/Write |
| 08 | Manufacturer ID | 129/x81 | | |

Information provided here is correct to the best of our knowledge.
Please report any errors or omissions, to info@digitrax.com

Return to Digitrax [Decoder Index Page](#)

Return to Digitrax [Home Page](#)

This page, and all contents, are Copyright (C) 2003 by Digitrax, Inc., Norcross, GA, USA.

Updated 01-15-03.